

Inline ECO uređaji:

| Naziv proizvoda | Oznaka proizvoda | Opis |
|------------------------|------------------|---|
| IB IL AI 4/I/4-20-ECO | 2702495 | 4 channel, 4...20mA analog input |
| IB IL AI 4/U/0-10-ECO | 2702496 | 4 channel, 0...10V analog input |
| | | |
| IB IL AO 4/I/4-20-ECO | 2702497 | 4 channel, 4...20mA analog output |
| IB IL AO 4/U/0-10-ECO | 2702498 | 4 channel, 0...10V analog output |
| | | |
| IB IL RTD 4/PT100-ECO | 2702499 | 4 channel, PT100 temperature acquisition |
| IB IL RTD 4/PT1000-ECO | 2702501 | 4 channel, PT1000 temperature acquisition |
| | | |
| IB IL UTH 4/J-ECO | 2702502 | 4 channel, thermoelement type J temperature acquisition |
| IB IL UTH 4/K-ECO | 2702503 | 4 channel, thermoelement type K temperature acquisition |
| IB IL UTH 4/L-ECO | 2702504 | 4 channel, thermoelement type L temperature acquisition |
| | | |
| IB IL RS 232-ECO | 2702795 | 1 channel serial communication RS232 |
| IB IL RS 485-ECO | 2702141 | 1 channel serial communication RS485 |
| | | |
| IB IL 24 DI 8/HD-ECO | 2702792 | 8 channel DI |
| IB IL 24 DO 8/HD-ECO | 2702793 | 8 channel DO |
| IB IL 24 DO 4/EF-ECO | 2702825 | 4 channel DI |
| | | |
| IB IL SAFE 2-ECO | 2702446 | 2 safe inputs, which can switch off the internal Us voltage |